



Pass and Seymour
Discontinued - Titan Series Magnetic Low-Voltage Dimmer, Black
Part No. CDLV703PBK



Slide Dimmer, Low Voltage, Single Pole/3Way PRESET 700VA, Black

Features & Benefits

Field configurable wall plate system.

Adjustable low end output voltage.

Rugged construction.

Simple to plan the rough-in.

Attractive European styling.

Exclusive adaptor kit to install other Decorator opening devices under the Titan: wall plate system.

For covering patents, see www.legrand.us/patents.

Labeling system.

Shipped with protective film.

Superior ratings with a minimum of de-rating when ganged.

Available in single pole slide-to-OFF and single pole/3-way preset models.

Eye-catching packaging.

Blank center plate included.

Specifications

General Info

| | | | |
|-------------------|--------------------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Black |
| Country Of Origin | China | Application Sector | Commercial |
| Standard | cULus, California Title 24 Compliant | Type | Dimmer |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|-------|--------------|-----|
| cULus ListingNumber | 95219 | cULus Listed | Yes |
|---------------------|-------|--------------|-----|

Technical Information

| | | | |
|------------------|--|--------------------------|---|
| Operating Cycles | 100 | Frequency Rating | 60 Hz |
| Amperage | 700 A | Voltage | 120.0 V |
| Load | Up to rating of device (including de-rating) | Environmental Conditions | Non-Condensing Humidity: Less than 95% |
