



C2G
10ft (3m) Serial RS232 DB9 Null Modem Cable with Low Profile Connectors M/M - In-Wall CMG-Rated
Part No. CG-52167

Audio/Video installations in educational and commercial settings often require in-wall rated cable. Our CMG-rated line was specifically engineered to meet this requirement while overcoming common challenges faced by installers in these environments. Low-Profile connectors (1.25 in total depth) save valuable space in the gang box, while the rounded shape accommodates smaller monitor mounts so that the cable can be easily hidden from view.



Specifically designed to support RS-232/Serial communications, this cable is fully shielded to prevent unwanted EMI/RFI interference. The fully molded cable design delivers excellent strain relief, while connector thumbscrews provide a quick and easy connection every time.

The transmit and receive signals are crossed to ensure proper data transmission.

CMG-rated cables meet with many NEC requirements for Communications Cables - General Purpose In Wall Use . Our cables meet the following ratings: CMG, FT4 (Canada)

Features & Benefits

Designed to support RS-232/Serial communications	CMG-rated for in-wall use
Shielded to prevent unwanted EMI/RFI interference	Connector thumbscrews for a quick and easy connection

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120521679	Country Of Origin	Vietnam
Features	RS232	Application Sector	Commercial, Industrial, Residential
Warranty Type	Lifetime	Type	Cable

Dimensions

Product Length US	10.0 FT	Cable Length	10 ft
-------------------	---------	--------------	-------

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	28 AWG
Jacket Application	In-Wall Rated	Cable Type	Modem, Serial
Jacket Rating	CMG Rated, FT4 Rated	Adapter Rear	DB9 Male
Adapter Front	DB9 Male		