



Legrand keyed LC fiber adapter panels are available in configurations that are keyed on the front only (user's side) or on both sides (user's and technician's) depending on the security requirements. Internal keying feature prevents tampering



Features & Benefits

Unique Key and Color Options: Up to thirteen unique keying options/colors for a wide range of network security systems, easy identification and network management.

Keyed front or Rear: Keyed LC adapters have the option to be keyed in the front only (user's side) or on both sides (user's and technician's) depending on the security requirements. Internal keying feature prevents tampering

Various Footprint Options: Keyed workstation adapter modules are available for TracJack® and High Density Jack (HDJ) style Face plates and surface mount boxes for complete system design flexibility.

Compatibility: All Legrand keyed LC fiber products are engineered to be compatible with other Legrand products to provide an end to end, data center to desktop solution.

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120298861	Country Of Origin	China
Features	Color-Coded	Application Sector	Commercial, Residential
Warranty Type	5-Year	Type	Active Device, Adapter, Adapter Ring

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Video Resolution	1080p, 4K, 4K 30Hz, 4K 60Hz
Cable Type	Adapter, Flexible	Adapter Rear	Lightning Male, USB-C Male, DisplayPort Male, Mini DisplayPort Male
Adapter Front	HDMI Female, HDMI Female, HDMI Female, HDMI Female	Operating Temperature	0°-40°C
Storage Temperature	-10° - 60° C		