

Cord Grip Male Straight, 2-1/2-inch NPT, 2.312-inch-2.437-inch



Features & Benefits

Deluxe cord grips are woven of stainless steel mesh with an aluminum body for corrosion resistance.

They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain.

They are recommended for indoor or outdoor use where subjected to moisture in the wiring of pendant stations, processing equipment, hand tools, and extension cord sets.

Deluxe grips are suitable for use in hazardous locations per Class I, Div. 2: Class II, Div. 1 & 2: and Class III, Div. 1 & 2.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007185379
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Cord Grip		

Dimensions

Cable Diameter Range 2.312-2.437 in

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

Technical Information

Maximum Cable Range	2.312 in	Grip Angle	Straight
Grip Fitting	Male	Minimum Cable Range	2.437 in
Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
NPT Thread Size	2-1/2 in	Mounting	Consult the Factory for Mounting Recommendations