



Pass and Seymour

**Discontinued - Nylon Strain Relief Cord Grip, 1-in NPT 90-Degree, .750-.875 OD Range, Stainless Steel Mesh**

Part No. CGN10090750M



## Features & Benefits

Heavy duty Nylon body is resistant to impact and corrosion

Available in straight, 90°, and underground feed styles

Rugged construction suitable for various industrial applications such as MRO, food processing, water/waste water, marine, pulp & paper, and petrochemical

Rubber grommet provides a liquid-tight seal and reduces cord pull-out while resisting chemicals

Color coded grommets make for easy identification and ease of installation

## Specifications

### General Info

|                    |                       |              |                 |
|--------------------|-----------------------|--------------|-----------------|
| Product Line       | Pass & Seymour        | UPC Number   | 785007057874    |
| Country Of Origin  | Mexico                | Construction | Nylon Cord Grip |
| Application Sector | Commercial/Industrial | Standard     | UL Listed       |

### Listing Agencies / 3rd Party Agencies

|            |     |
|------------|-----|
| CSA Listed | Yes |
|------------|-----|

### Technical Information

|                     |         |                     |          |
|---------------------|---------|---------------------|----------|
| Maximum Cable Range | 0.75 in | Minimum Cable Range | 0.875 in |
|---------------------|---------|---------------------|----------|