



Pass and Seymour  
Nylon Strain Relief Cord Grip, 3/4-in NPT 90-Degree, .625-.750 OD Range, Nylon Mesh  
Part No. CGN7590625NM

Non-Metallic Cord Connectors are constructed of a durable, nylon material which offers excellent corrosion resistance, is lightweight, durable and ideal for use in damp environments. Nylon Cord Connectors are ideally suited for use in applications with moisture or washdowns and they provide an environmental seal against dirt, coolants, as well as other chemicals.



## Features & Benefits

Heavy duty Nylon body is resistant to impact and corrosion

Available in straight, 90°, and underground feed styles

Rugged construction suitable for various industrial applications such as MRO, food processing, water/waste water, marine, pulp & paper, and petrochemical

Rubber grommet provides a liquid-tight seal and reduces cord pull-out while resisting chemicals

Color coded grommets make for easy identification and ease of installation

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007059014
Country Of Origin	Mexico	Construction	Nylon Cord Grip
Application Sector	Commercial/Industrial	Standard	UL Listed

### Listing Agencies / 3rd Party Agencies

CSA Listed Yes

### Technical Information

Maximum Cable Range 0.625 in Minimum Cable Range 0.75 in