



## Legrand

Stainless Steel Strain Relief Cord Grip, 3/4" Straight, .68-.81 OD Range  
Part No. CGSS75812M

Stainless Steel Strain Relief Cord Grips are woven of stainless steel mesh with a Type 304 stainless steel body for corrosion resistance. They are offered in single/double weave construction to help absorb direct pull, to resist flexing and binding, and to eliminate strain. They are recommended for indoor or outdoor use where subjected to moisture and corrosion in the wiring of pendant stations, processing equipment, hand tools, and power cord sets.



### Features & Benefits

304 grade Stainless Steel body and mesh construction provides exceptional tensile strength and resists corrosion and impacts Includes an embedded Buna-N O-Ring providing a long-term seal and protection against ingress

The combination tightening surface provides a large wrenching area for easy installation

Available in straight male fittings from 1/2" to 3" NPT

Also available in 316 grade stainless steel, upon request. Minimums may apply

### Specifications

#### General Info

UPC Number 785007107999

Country Of Origin United States

Product Line Pass & Seymour

Application Sector Commercial/Industrial

Construction Stainless Steel Cord Grip

Standard UL Listed, CSA Listed

#### Technical Information

Cable Size .68 - .81