



The ball camera is an inconspicuous way to monitor a nursery, patio, or front door. Although it delivers crisp color video, it's also optimized for low light conditions to enable the best possible pictures in all situations. It ships with Studio style

Features & Benefits

Provides smooth, 720P Hi-Definition at 30 frames per second (FPS)

Picture automatically changes to black and white at night to optimize for low light conditions

Includes Studio style plates for both in-wall and in-ceiling installation.

Weather resistant for outdoor applications.

Mounts in a standard single gang box with a convenient RJ45 connection.

Specifications

General Info

Product Line	On-Q	UPC Number	804428030713
Country Of Origin	China	Application Sector	Residential

Technical Information

IP/Analog	Analog	Effective Pixels	512 MP
Power Supply	POE from camera module (DC12.0V \pm 1.0V, 90-100mA) (not included)	Image Features	Color, Auto Sensing Iris changes to black and white for night time viewing
Resolution	420 TVL (H) X 480 TVL (V)	Electronic Shutter Speed	1 s, 0 s
Minimum Illumination	0.5 lm	Vertical Viewing Angle	90 deg
Day/Night	Day/Night		