



The ball camera is an inconspicuous way to monitor a nursery, patio, or front door. Although it delivers crisp color video, it's also optimized for low light conditions to enable the best possible pictures in all situations. It ships with Studio style

## Features & Benefits

Provides smooth, 720P Hi-Definition at 30 frames per second (FPS)

Picture automatically changes to black and white at night to optimize for low light conditions

Includes Studio style plates for both in-wall and in-ceiling installation.

Weather resistant for outdoor applications.

Mounts in a standard single gang box with a convenient RJ45 connection.

## Specifications

### General Info

|                   |       |                    |              |
|-------------------|-------|--------------------|--------------|
| Product Line      | On-Q  | UPC Number         | 804428030799 |
| Country Of Origin | China | Application Sector | Residential  |

### Technical Information

|                      |  |                          |   |
|----------------------|--|--------------------------|---|
| IP/Analog            | Analog   | Effective Pixels         | 512 MP  |
| Power Supply         | POE from camera module (DC12.0V $\pm$ 1.0V, 90-100mA) (not included) | Image Features           | Color, Auto Sensing<br>Iris changes to black and white for night time viewing |
| Resolution           | 420 TVL (H) X 480 TVL (V)  | Electronic Shutter Speed | 1 s, 0 s  |
| Minimum Illumination | 0.5 lm   | Vertical Viewing Angle   | 90 deg  |
| Day/Night            | Day/Night  |                          |   |