



On-Q  
Discontinued - Outdoor 1080 IR Dome Camera with Zoom  
Part No. CM7020



Keep a watchful eye on your home with Legrand's CM7020 Dome Camera. It delivers full 1080p HD and has professional-grade night vision. The durable dome housing is vandal and weather resistant and the varifocal lens allows for motorized remote zooming.

## Features & Benefits

Enclosure-mounted recording solution for up to four IP cameras	4 MP image supports 16x9 wide frame with full 1080P HD resolution.
Motorized varifocal lens for flexible remote zooming without loss of resolution.	Vandal and weather resistant dome camera body for indoor and outdoor use.
Professional-grade night vision allows users to see up to 50 feet clearly in near total darkness.	Easily install over a single-gang electrical box.
Powered by a single PoE cable.	Support for 32GB MicroSD storage for basic recording and extended recording with Legrand Network Video Recorder.
Compatible with Intuity Home Automation	

## Specifications

### General Info

Product Line	On-Q	UPC Number	804428431428
Country Of Origin	China	Application Sector	Residential
Standard	FCC Part 15 Class B, RoHS		

### Listing Agencies / 3rd Party Agencies

FCC Compliant	Yes
---------------	-----

### Additional Information

RoHS Conformant	Yes
-----------------	-----

---

Technical Information

IP/Analog	IP	Frame Rate	30 fps
Effective Pixels	4 MP	Zoom Ratio	2.8
Resolution	2688 x 1520 @ 30 fps / 1920 x 1080 @ 30 fps / 1280 x 720 @ 30 fps / 640 x 360 @ fps	Auto Iris Type	2.8 to 8mm, 2.8X motorized lens @ F1 (8mm)
Vertical Viewing Angle	50.25 deg		

---