



**On-Q**  
**Outdoor 1080 IR Dome Camera with Zoom**  
Part No. CM7020



Keep a watchful eye on your home with Legrand's CM7020 Dome Camera. It delivers full 1080p HD and has professional-grade night vision. The durable dome housing is vandal and weather resistant and the varifocal lens allows for motorized remote zooming.

## Features & Benefits

View live feed and receive email alerts with the Legrand Camera app for iOS and Android devices.

4 MP image supports 16x9 wide frame with full 1080P HD resolution.

Motorized varifocal lens for flexible remote zooming without loss of resolution.

Vandal and weather resistant dome camera body for indoor and outdoor use.

Professional-grade night vision allows users to see up to 50 feet clearly in near total darkness.

Easily install over a single-gang electrical box.

Powered by a single PoE cable.

Support for 32GB MicroSD storage for basic recording and extended recording with Legrand Network Video Recorder.

Compatible with Intuity Home Automation

## Specifications

### General Info

UPC Number	804428431428	Country Of Origin	China
------------	--------------	-------------------	-------

Product Line	On-Q	Application Sector	Residential
--------------	------	--------------------	-------------

Standard	FCC Part 15 Class B, RoHS
----------	---------------------------

### Additional Information

RoHS Conformant	Yes
-----------------	-----

### Technical Information

---

Vertical Viewing Angle	50.25 deg	Zoom Ratio	2.8
IP/Analog	IP	Auto Iris Type	2.8 to 8mm, 2.8X motorized lens @ F1 (8mm)
Effective Pixels	4 MP	Resolution	2688 x 1520 @ 30 fps / 1920 x 1080 @ 30 fps / 1280 x 720 @ 30 fps / 640 x 360 @ fps
Frame Rate	30 fps		

---