



Pass and Seymour

Discontinued - 1200 Series Cable Reel with Flying Lead 10 Amp, 16 AWG, 35 ft For Lift/Drag Applications

Part No. CR12L163N35F10B



Industrial-grade 1200 Series Cable Reels are precision machines, built with a minimum of components to provide years of reliable service with little or no maintenance. Made of all steel construction in the USA, these cable rels are ideal for assembly and fabrication work areas, conveyors, utility trucks, automotive and truck work bays, and much more.

Features & Benefits

- Made in USA
- All steel construction with fiberglass/nylon drum, yellow powder coat finish
- UL/CSA Listed

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007205992	Country Of Origin	United States
Features	Lift/Drag, Retractable	Application Sector	Commercial, Data Center, Education, Industrial
Warranty Type	1-Year	Type	Cable Reel

Technical Information

Wire Gauge	16 AWG	Cord Length	35 ft
Amperage	10 A	Number of Conductors	3
Indoor/Outdoor	Indoor	Mobile End	Flying Lead
Operating Temperature	22°-194°F	Voltage	125.0 V