



Pass and Seymour
Discontinued - 1400 Series Cable Reel with Flying Lead 10 Amp, 16 AWG, 100 feet For Lift/Drag Applications
Part No. CR14L163N100F10



Features & Benefits

UL and CSA Listed	Steel frame construction, black thermoplastic slip ring cover, yellow powder-coat finish
NEMA 4 rated enclosure	1788

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	CR14L163N70F10
Color	Yellow	UPC Number	785007206555
Country Of Origin	United States	Features	Lift/Drag, Retractable
Application Sector	Commercial, Data Center, Education, Industrial	Warranty Type	1-Year
Type	Cable Reel		

Technical Information

Wire Gauge	16 AWG	Cord Length	100 ft
Amperage	10 A	Number of Conductors	3
Indoor/Outdoor	Both	Mobile End	Flying Lead
Operating Temperature	22°-194°F	Voltage	600.0 V