



Pass and Seymour  
Discontinued - 1400 Series Cable Reel with Flying Lead, 20 Amp, 10 AWG, 60 feet, For Retrieval Applications | Sub CR14L104N40F20B  
Part No. CR14R104N60F20B



Features & Benefits

UL and CSA Listed	Steel frame construction, black thermoplastic slip ring cover, yellow powder-coat finish
NEMA 4 rated enclosure	1788

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	CR14L104N40F20B
Color	Black	UPC Number	785007206159
Country Of Origin	United States	Features	Retractable, Retrieve
Application Sector	Commercial, Data Center, Education, Industrial	Warranty Type	1-Year
Type	Cable Reel		

Technical Information

Cord Length	60 ft	Amperage	20 A
Number of Conductors	4	Indoor/Outdoor	Both
Mobile End	Flying Lead	Operating Temperature	22°-194°F
Voltage	600.0 V		