

Turnlok Connector 3wire 30amp 250volt Corrosion Resistant



Features & Benefits

Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.	Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
Raised ribs provide non-slip gripping profile for turning to lock and unlock.	Double dovetail design provides superior protection against cord pull-out forces.
Impact- and corrosion-resistant durable nylon 6 shell material.	Rounded back contour reduces snags and hang-ups on the job site.
Scallop shell design provides non-slip gripping surface for insertion and withdrawal.	Visible stamped NEMA configuration and device rating.
New-design external cord grips provide visible assurance of safe and proper cord retention.	Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

Specifications

General Info

Color	Yellow	UPC Number	785007263084
Country Of Origin	Mexico	Product Line	Pass & Seymour
Application Sector	Industrial	Standard	UL Listed

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	cULus ListingNumber	146159
--------------	-----	---------------------	--------

Technical Information

Number of Poles	Double Pole	Voltage	250 V
Phase	3	Number of Wires	3