



Commercial 3-Way Switch, Side-Wire, 20A 120/277V.

These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse.

Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|-------------------|-------------------------------------------------------------------------------|--------------------|--------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007126556 |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2, | Type | Switch |

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|-----------------------|-----------------------------------|----------|--------|
| Contact Configuration | One piece brass alloy contact arm | Actuator | Toggle |
|-----------------------|-----------------------------------|----------|--------|

| | | | |
|------------|--------------------------------------------|----------------|---------------------------------|
| Connection | Side Wire or external screw-pressure plate | Contact Rating | Oversized silver alloy contacts |
|------------|--------------------------------------------|----------------|---------------------------------|

| | | | |
|-----------------|-------|----------------|--------|
| Number of Poles | 3-Way | Indoor/Outdoor | Indoor |
|-----------------|-------|----------------|--------|

| | | | |
|-----------------------|----------------|---------|------------------|
| Operating Temperature | -40° to 115° C | Voltage | 120 VAC, 277 VAC |
|-----------------------|----------------|---------|------------------|

| | | | |
|-----------------|-------|----------------------|------------------------------------|
| Connection Type | Wired | Degree of Protection | 1500V Dielectric Withstand Voltage |
|-----------------|-------|----------------------|------------------------------------|
