



Pass and Seymour  
Hard Use Specification Grade Switch, Light Almond  
Part No. CSB15AC3LA



Construction 3-Way Switch, Back and Side-Wire, 15A 120/277V.

## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 - #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

|                    |                |                   |        |
|--------------------|----------------|-------------------|--------|
| Product Line       | Pass & Seymour | Country Of Origin | Mexico |
| Application Sector | Commercial     | Standard          | UL 20  |

### Dimensions

|                   |          |                  |          |
|-------------------|----------|------------------|----------|
| Product Width US  | 1.32 in  | Product Depth US | 1.073 in |
| Product Height US | 3.281 in |                  |          |

---

## Listing Agencies / 3rd Party Agencies

---

|                     |        |              |     |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140597 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

---

## Technical Information

---

|                |                   |                           |        |
|----------------|-------------------|---------------------------|--------|
| Contact Rating | 120/277vac, 15amp | Closed Contact Resistance | Toggle |
|----------------|-------------------|---------------------------|--------|

---

|          |      |                 |       |
|----------|------|-----------------|-------|
| Amperage | 15 A | Number of Poles | 3-Way |
|----------|------|-----------------|-------|

---

|         |     |         |         |
|---------|-----|---------|---------|
| Wattage | 3 W | Voltage | 120.0 V |
|---------|-----|---------|---------|

---