



Pass and Seymour  
Hard Use 20A Specification Grade Toggle Switch, Brown  
Part No. CSB20AC3



Construction 3-Way Switch, Back and Side-Wire, 20A 120/277V. These switches offer excellent value while meeting federal specification standards. External screw-pressure-plate back wiring enables fast installation and superior electrical connections. Rugged construction shrugs off hard use and abuse.

## Features & Benefits

One-piece brass alloy contact arm for reliable electrical performance.

High strength thermoplastic polycarbonate toggle resists breaking and chipping under heavy abuse.

Back body made of glass-reinforced nylon. Locking support provides resistance to face and back body separation.

Cam designed for fast make with positive break action to minimize arcing and prolong switch life.

Tri-drive terminal and mounting screws.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

One-piece steel strap with integral ground is plated for corrosion resistance.

Heavy-duty toggle bumpers for smooth and quiet operation.

Available with side wire or external screw-pressure-plate back and side wire models capable of accepting #14 to #10 AWG copper or copper-clad wire.

Oversized silver alloy contacts for longer dependable switch life.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	Country Of Origin	Mexico
Application Sector	Residential/Commercial	Standard	UL Listed E140597, Standard UL20, FedSpec WS896, Flammability Rating UL94 V2
Type	Switch		

---

## Dimensions

---

Product Width US	1.32 in	Product Depth US	1.073 in
------------------	---------	------------------	----------

---

Product Height US	3.281 in
-------------------	----------

---

## Listing Agencies / 3rd Party Agencies

---

cULus ListingNumber	140597	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Contact Configuration	One piece brass alloy contact arm	Actuator	Toggle
-----------------------	-----------------------------------	----------	--------

---

Connection	Side Wire or external screw-pressure plate	Contact Rating	Oversized silver alloy contacts
------------	--	----------------	---------------------------------

---

Amperage	20 A	Number of Poles	3-Way
----------	------	-----------------	-------

---

Indoor/Outdoor	Indoor	Operating Temperature	-40°-115°C
----------------	--------	-----------------------	------------

---

Voltage	120/277 V	Connection Type	Wired
---------	-----------	-----------------	-------

---

Degree of Protection	1500V Dielectric Withstand Voltage
----------------------	------------------------------------

---