



Ortronics

Discontinued - Cisco CWDM-SFP-1330-40 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1330nm, 40km, LC Duplex, DDM, I-Temp)
Part No. CWDM-SFP-1330-40-L



Cisco CWDM-SFP-1330-40 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1330nm, 40km, LC Duplex, DDM, I-Temp)

Features & Benefits

Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Specifications

General Info

| | | | |
|-------------------|-------------|---------------|--------------|
| Product Line | Ortronics | UPC Number | 662875060086 |
| Country Of Origin | China | Warranty Type | Lifetime |
| Type | Transceiver | | |

Dimensions

| | | | |
|-------------------|---------|------------------|---------|
| Product Width US | 13.9 mm | Product Depth US | 58.4 mm |
| Product Height US | 8.5 mm | | |

Technical Information

| | | | |
|---------------------------|-------------|---------------------------|-------|
| Fiber Optic Cable Type | Single-Mode | Max Distance Support | 40 km |
| Operating Temperature Min | -40 °C | Operating Temperature Max | 85 °C |
| Connector Type | LC Duplex | Form Factor | SFP |