



Ortronics

Discontinued - Cisco CWDM-SFP-1590-40 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1590nm, 40km, LC Duplex, DDM, I-Temp)
Part No. CWDM-SFP-1590-40-L



Cisco CWDM-SFP-1590-40 Compatible 1000Base-CWDM SFP Transceiver (SMF, 1590nm, 40km, LC Duplex, DDM, I-Temp)

Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty: For more information by product line, visit our [Warranty page](#).

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

Industry Leading Lifetime Warranty: For more information by product line, visit our [Warranty page](#).

Specifications

General Info

Product Line	Ortronics	UPC Number	662875060475
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		

Dimensions

Product Width US	13.9 mm	Product Depth US	58.4 mm
Product Height US	8.5 mm		

Technical Information

Fiber Optic Cable Type	Single-Mode	Max Distance Support	40 km
Operating Temperature Min	-40 °C	Operating Temperature Max	85 °C
Connector Type	LC Duplex	Form Factor	SFP