



Gator Grip Connector, 2-Pole 3-Wire 50A 125V Grounding, Yellow

Features & Benefits

Gator Grip Jaws grab cord tighter as you hand turn the housing.

Nylon jaws grip securely, but won't damage insulation.

Self-locking Dardet Thread holds securely and assures firm clamping.

Fast wiring -- simply insert stranded conductors into individual wiring chambers and tighten oversized terminal screws.

Transparent wiring chamber cover allows visual inspection of wiring chambers to assure proper connections.

Sloped shoulders won't catch or snap.

Automatic cord centering.

Brilliant high-visibility yellow.

Neoprene Dust Seal helps keep out dirt and debris.

Dead front construction.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	Mexico	Application Sector	Commercial
Standard	UL 498	Type	Straight Blade

Dimensions

Product Width US	2.63 in	Product Length US	3.57 in
------------------	---------	-------------------	---------

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Number of Wires	15	Amperage	50 A
-----------------	----	----------	------

Number of Poles	Double Pole	Wire Size	18 - 10 AWG
-----------------	-------------	-----------	-------------

Voltage	125.0 V
---------	---------
