



Gator GripConnector, 2-Pole 3-Wire 50A 250V Grounding, Yellow

Features & Benefits

Gator Grip Jaws grab cord tighter as you hand turn the housing.

Fast wiring -- simply insert stranded conductors into individual wiring chambers and tighten oversized terminal screws.

Sloped shoulders won't catch or snap.

Brilliant high-visibility yellow.

Dead front construction.

Nylon jaws grip securely, but won't damage insulation. Self-locking Dardelet Thread holds securely and assures firm clamping.

Transparent wiring chamber cover allows visual inspection of wiring chambers to assure proper connections.

Automatic cord centering.

Neoprene Dust Seal helps keep out dirt and debris.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Yellow
Country Of Origin	Mexico	Standard	UL 498

Dimensions

Product Width US	2.63 in	Product Length US	3.57 in
------------------	---------	-------------------	---------

Technical Information

Connection	Wire Grounding	Number of Wires	3
------------	----------------	-----------------	---

Amperage	50 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	4	Voltage	250.0 V
-----------	---	---------	---------
