



Wiremold
Cord Ended deQuorum™ Single Flip Up Unit with USB
Part No. DQFP15UBK



Unit includes one (1) 15A black tamper-resistant duplex receptacle with two (2) USB ports that provide 3.1A. Unit comes with a 6' (1.83m) cord. Comes with a black powder coat finish.

Features & Benefits

Sleek, Attractive Design: Slimmer, lower profile integrates well with table surfaces to enhance conference rooms, meeting rooms, hotel rooms, kitchens, and offices.

Tamper-Resistant Receptacles: Meets 2011 NEC TamperResistant requirements. Receptacles feature our patented shutter system that prevents the insertion of foreign objects for safety.

New Soft Opening Cover Mechanism: Opening and closing the cover is quieter and easier with a more professional feel.

Expanded Configuration Options: Accepts full size receptacles which provides expanded custom flexibility. Consult factory for more information.

UL Spill Water Protection: Meets and exceeds UL1363 standard for relocatable power taps. Eliminates risk of shock or short circuiting due to moisture entering device.

USB Charging Capability: Duplex 3.1A USB receptacles provide charging capacity for a wide range of mobile devices.

Multiple Cover Finish Options: Durable black powder coat and brushed stainless steel finishes blend with most decors.

cULus Listed: Meets UL US and Canadian safety standards for Relocatable Power Taps (File E66421, Guide XYBS) and Multitoutlet Assemblies (File E15191, Guide PVGT).

Specifications

General Info

Product Line	Wiremold	Country Of Origin	Mexico
Construction	Die Cast	Application Sector	Residential/Commercial
Standard	cULus Listed Relocatable Power Tap: File E66421 Guide XYBS, cULus Listed Multioutlet Assembly: File E15191 Guide PVGT, Meets Article 380 of NEC	Type	Flip Up

Dimensions

Product Width US	4.75 in	Product Length US	5.625 in
------------------	---------	-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Buy American Act Compliance

NAFTA Yes

Additional Information

RoHS Conformant Yes

Technical Information

Cable Entry Below Mounting Type Recessed

Number of Outlets 2