



Preset Decorator Rotary Dimmer, Single Pole/3-way/1100W with pilot light, Ivory

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
Country Of Origin	China	Application Sector	Residential/Commercial
Standard	UL/CSA Listed	Type	Dimmer

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

### Technical Information

Operating Cycles	100000	Frequency Rating	60 Hz
Amperage	4.5 A	Number of Poles	Single Pole
Wattage	1100 W	Voltage	120.0 V
Load	1100watt		