



Ortronics

Cisco DS-SFP8G-ZR Compatible 10GBase-ZR SFP+ Transceiver (SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp)

Part No. DS-SFP8G-ZR-L



Cisco DS-SFP8G-ZR Compatible 10GBase-ZR SFP+ Transceiver (SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp)

## Features & Benefits

### Guaranteed Compatible

In System tested in over 90 OEM switches, routers and servers.

### 99.98% Reliability Rate

Functionally, optically and environmentally tested to exact specifications.

### Industry Leading Lifetime Warranty

For more information by product line, visit our Warranty page.

### 98% On-Time Delivery Rate

Extensive inventory guarantees same day shipping.

### Full Service Technical Support

Call, chat, email or meet for expert optical connectivity support.

## Specifications

### General Info

Product Line	Ortronics	Country Of Origin	China
Warranty Type	Lifetime	Type	Transceiver

### Technical Information

Fiber Optic Cable Type	Single-Mode	Operating Temperature Min	-40 C
Operating Temperature Max	85 C	Data Transfer Rate	10 Gbps
Connector Type	LC Duplex	Wavelength	1550nm
Form Factor	SFP+		