



# On-Q

20" Enclosure (no cover)  
Part No. EN2080



This 20" enclosure features universal On-Q bay-style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more side lances, and side tabs for

## Features & Benefits

- Flanged covers hide drywall openings
- Drywall depth indicators
- Flush and surface installation
- Mounting tabs provide correct flush-mount position for standard installations
- Patented mounting system offers versatile module mounting options
- Literature pouch included for dealer information
- Includes self-adhesive cable identification table
- Made in the USA

## Specifications

### General Info

UPC Number	804428023104	Country Of Origin	United States
Product Line	On-Q	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS		

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes	CSA Listed	Yes
--------------	-----	------------	-----

### Additional Information

RoHS Conformant	Yes
-----------------	-----

### Technical Information

Cable Entry	{6} rear knockouts, {3} top knockouts, {2} rectangular knockouts for 1-gang electrical box in	Thickness	0.1 in
Frame	Cold Rolled Steel		