



**On-Q**  
**42-inch Enclosure with Hinged Door**  
Part No. EN4250



Perfect for larger installations, this 42" enclosure features universal On-Q style mounting holes that are compatible with all bay-style modules. It also includes larger top openings that make pulling wire easier as well as additional knockouts, more s

## Features & Benefits

42-in Enclosure with Hinged Door	Drywall depth indicators
Flush and surface installation	Mounting tabs provide correct flush-mount position for standard installations
Patented mounting system offers versatile module mounting options	Literature pouch included for dealer information
Includes self-adhesive cable identification table	Cover included
Made in the USA	

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428023180	Country Of Origin	United States
Package Quantity	1	Application Sector	Residential
Standard	UL (UL985, UL1023, UL1863), cULus, CSA, RoHS	Type	Enclosure

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	cULus Listed	Yes
------------	-----	--------------	-----

### Additional Information

---

RoHS Conformant Yes

Product Environmental Profile Yes

---

### Technical Information

---

Thickness 0.1 in

Enclosure Type

Traditional

---

Cable Entry (6) rear knockouts, (3) top knockouts, (2) rectangular knockouts for 1-gang electrical box in

Frame

Cold Rolled Steel

---