



On-Q

**9-inch Dual-Purpose In-Wall Enclosure with 5-inch Mounting Plate**

Part No. ENP0905NAV1



The 9-inch Dual-Purpose In-Wall Enclosure is engineered to provide storage of structured wiring and AV components. The ENP0905NAV1 is constructed of Wi-Fi transparent material to manage wireless components and AV devices at point-of-use locations, like directly behind a TV or other media centers. It can also be used for structured wiring purposes, such as networking equipment, access points, switches and more. The ENP0905NAV1 is compatible with devices like Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more. Includes a 5-inch elevated mounting plate, cover, trim ring and drywall clips, allowing for both new construction and retrofit installations.

## Features & Benefits

Replacement trim ring and cover

Can be placed behind most TV wall-mounts including SANUS premium TV mounts

Compatible with devices like Apple TV, Roku, Amazon Fire TV, network switches, 3rd party structured wiring components and more

Comes with removable mounting plate that features 1.5-in of elevation to accommodate larger devices and frees up space in the enclosure

Tool-free cover is low profile and designed to snap into place providing a "flush" appearance to wall surface

Knockout configurations support conduit and in-wall wired connections, while a cable pass through on cover allows for outside cable connections

Features (2) AC knockouts to accommodate a single gang junction box to power devices in enclosure

Universal mounting grid maximizes compatibility with 3rd party devices without additional mounting brackets

Features drywall clips to allow both retrofit and new construction installations

UL Listed and constructed of Wi-Fi transparent ABS plastic to ensure uninterrupted performance of wireless devices

Proudly made in the USA

## Specifications

### General Info

Product Line	On-Q	Color	White
UPC Number	804428434139	Country Of Origin	United States
Application Sector	Commercial, Residential	Standard	RoHS, UL, cULus
Type	Enclosure		

### Dimensions

---

Product Width US 14.37 in Product Depth US 3.88 in

---

Product Height US 9.33 in

---

#### **Listing Agencies / 3rd Party Agencies**

---

cULus Listed Yes

---

#### **Additional Information**

---

RoHS Compliant Yes

---

#### **Technical Information**

---

Compatibility	Paintable with Rust-Oleum paint for plastic or equivalent	Seismic Tested	No
---------------	---	----------------	----

---

Thickness	0.1 in	Enclosure Type	Dual Purpose
-----------	--------	----------------	--------------

---

Frame	Injection-molded plastic	Mounting	Consult the Factory for Mounting Recommendations
-------	--------------------------	----------	--

---

Environmental Conditions	0 to 93% (relative humidity, non-condensing)
--------------------------	--

---