



10GBase-ZR XFP Compatible Transceiver SMF, 1550nm, 80km, LC Duplex, DDM, I-Temp

Features & Benefits

- Guaranteed Compatible: In System tested in over 90 OEM switches, routers and servers.

Industry Leading Lifetime Warranty: For more information by product line, visit our Warranty page.

Full Service Technical Support: Call, chat, email or meet for expert optical connectivity support.
- 99.98% Reliability Rate: Functionally, optically and environmentally tested to exact specifications.

98% On-Time Delivery Rate: Extensive inventory guarantees same day shipping.

Specifications

General Info			
Product Line	Ortronics	UPC Number	662875076971
Country Of Origin	China	Warranty Type	Lifetime
Type	Transceiver		
Dimensions			
Product Width US	16.3 mm	Product Depth US	78.0 mm
Product Height US	8.4 mm		
Technical Information			
Fiber Optic Cable Type	Single-Mode	Max Distance Support	80 km
Operating Temperature Min	-40 °C	Operating Temperature Max	85 °C
Data Transfer Rate	10 Gbps	Connector Type	LC Duplex