



Pass and Seymour  
**1-Gang Tamper-Resistant Floor Box Assembly (for Wood Sub-Floors)**  
Part No. FB1TRDRB



Tamper-Resistant Floor Box Assembly, #8 duplex opening. Two threaded screw plugs, Includes 3232 15A, 125A tamper-resistant receptacle. Brass.

## Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.	Rugged diecast cover plates.
Meets UL514(c) and NEC 314.27(c).	Scrub water compliant.
With durable nickel or brass cover plates.	Dual-voltage models available.
Swing brackets mounting option eliminates drilling tile flooring for mounting screws.	Wood sub-floors only.
Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brass
UPC Number	785007108750	Country Of Origin	Mexico
Features	Durable	Installation Location	Underfloor
Application Sector	Commercial, Residential	Standard	UL listed
Warranty Type	1-Year Limited Warranty	Type	Floor Box

### Dimensions

Cubic Capacity	20.5 in³
----------------	----------

### Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

---

Technical Information

---

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Rectangular
Mounting Type	Screw Mount		

---