



Pass and Seymour
Tamper-Resistant Floor Box Assembly - One Gang for Wood Sub-Floors, Brass
Part No. FB1TRSRB



Tamper-Resistant 1-Gang Floor Box Assembly. Single threaded screw plug. Includes 15A, 120 volts tamper-resistant single receptacle. Brass. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.	Rugged diecast cover plates.
Meets UL514(c) and NEC 314.27(c).	Scrub water compliant.
With durable nickel or brass cover plates.	Dual-voltage models available.
Swing brackets mounting option eliminates drilling tile flooring for mounting screws.	Wood sub-floors only.
Wire Fill (AWG): 10 No. 14, 9 No. 12, 8 No. 10.	

Specifications

General Info

Product Line	Pass & Seymour	Color	Brass
UPC Number	785007108712	Country Of Origin	United States
Features	Durable	Installation Location	Underfloor
Application Sector	Commercial, Residential	Standard	Residential/Commercial
Warranty Type	1-Year Limited Warranty	Type	Floor Box

Dimensions

Cubic Capacity	20.5 in³
----------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Rectangular
Mounting Type	Screw Mount		