



Pass and Seymour
Tamper-Resistant Floor Box Assembly - Two Gang for Wood Sub-Floors
Part No. FB2TRDR2N



Tamper-Resistant Floor Box Assembly, Two #8 duplex openings, Four threaded screw plugs. Includes two 3232 15A, 125A tamper-resistant duplex receptacles. Nickel. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Tamper-Resistant shutters let plugs in, keep other things out.

Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors.

Large box flange rests on finished floor -- no adjustments needed.

Extra-deep design leaves plenty of wiring room.
- Rugged diecast cover plates with durable nickel or brass finish.

Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.

Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.

Specifications

General Info

Product Line	Pass & Seymour	Color	Nickel
UPC Number	785007108699	Country Of Origin	United States
Features	Durable	Installation Location	Underfloor
Application Sector	Commercial, Residential	Standard	UL Listed
Warranty Type	1-Year Limited Warranty	Type	Floor Box

Dimensions

Cubic Capacity	42.5 in³
----------------	----------

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

Number of Gangs	2	Indoor/Outdoor	Indoor
Cable Entry	Back	Box Shape	Rectangular
Mounting Type	Screw Mount		
