



Pass and Seymour
Tamper-Resistant Floor Box Assembly - Two Gang for Wood Sub-Floors
Part No. FB2TRDR2N



Tamper-Resistant Floor Box Assembly, Two #8 duplex openings, Four threaded screw plugs. Includes two 3232 15A, 125A tamper-resistant duplex receptacles. Nickel. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

- Tamper-Resistant shutters let plugs in, keep other things out.

Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors.

Large box flange rests on finished floor -- no adjustments needed.

Extra-deep design leaves plenty of wiring room.
- Rugged diecast cover plates with durable nickel or brass finish.

Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.

Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.

Specifications

General Info

Product Line	Pass & Seymour	Country Of Origin	United States
Construction	Wood Floor	Application Sector	Residential/Commercial
Standard	UL Listed		

Dimensions

Cubic Capacity	42.5 cu in
----------------	------------

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Outlets	2
---------------------	-----	-------------------	---
