



Legrand

Tamper-Resistant Floor Box Assembly - Two Gang for Wood Sub-Floors
Part No. FB2TRDRKS4B



Tamper-Resistant Floor Box Assembly, Dual-voltage. Two #8 duplex openings, Four threaded screw plugs. Includes 3232 15 amp, 125 volt tamper-resistant duplex receptacle, Cat5E Jack, F-connector, Ten Blanks and a low-voltage divider. Brass. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Tamper-Resistant shutters let plugs in, keep other things out.

Meets UL514(c) and NEC 314.27(c) requirements including scrub water for tile floors.

Large box flange rests on finished floor -- no adjustments needed.

Extra-deep design leaves plenty of wiring room.

Rugged diecast cover plates with durable nickel or brass finish.

Scrub water compliant without caulking, supplied with foam gasket and O-ring-equipped plugs.

Swing brackets mounting, great for tile floors -- eliminates drilling for mounting screws.

Includes 15 Amp, 125 Volt tamper-resistant duplex receptacle, low-voltage divider, Cat 5e jack, F-connector, and blanks.

Specifications

General Info

Color Brass

UPC Number 785007108743

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Residential/Commercial

Construction Wood Floor

Standard UL Listed

Dimensions

Cubic Capacity 42.5 cu in

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Technical Information

