



**Pass and Seymour**  
**Support Grips Standard Duty, Closed Mesh**  
 Part No. FC050UU



Standard-duty, Closed mesh, Double eye grips. Cable diameter - 0.500-0.610", Bale length - 4", Mesh length - 11", Break strength - 770 lbs.

## Features & Benefits

Standard closed mesh support grips are designed for loads up to 600 lbs. Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing. Closed mesh support grips are used when the end of the cable is accessible.

Support grips are woven of corrosion-resistant tinned-bronze wire. Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

## Specifications

### General Info

UPC Number	785007980998	Country Of Origin	Mexico
Product Line	Pass & Seymour	Application Sector	Industrial
Construction	Various Types of Pulling, Support and Strain Relief Grips	Standard	UL/CSA Approval (consult factory)

### Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

### Technical Information

Mounting	Consult the Factory for Mounting Recommendations	Cable Size	Cable Dia. Range: 0.500-0.610: Bale Length: 4: Mesh Length: 11
Capacity	Various Cable Diameter Ranges	Load	Approx. Break Strength: 770