



FC075LB: Standard Duty, Closed Mesh, Locking Bale (Universal Eye), Cable Diameter 0.75 - 0.99 inches, Bale Length 18-in, Mesh Length 14-in, Break Strength 1320 lbs.

Features & Benefits

- Closed mesh support grips are used when the end of the cable is accessible.
Standard duty closed mesh support grips are designed for loads up to 600 lbs.
- Vertical runs of no more than 100 ft.
They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.
- Support grips are woven of corrosion-resistant tinned-stainless steel wire.
Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007980028
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 0.750-0.990: Bale Length: 18: Mesh Length: 14
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 1,320