



Pass and Seymour
Support Grips Standard Duty, Closed Mesh
 Part No. FC150OF



Standard-duty, Closed mesh, Offset eye grips. Cable diameter - 1.500-1.740-inch, Bale length - 5-inch, Mesh length - 18-inch, Break strength - 1,680 lbs.

Features & Benefits

Standard closed mesh support grips are designed for loads up to 600 lbs. Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing. Closed mesh support grips are used when the end of the cable is accessible.

Support grips are woven of corrosion-resistant tinned-bronze wire. Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007980387
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes	CSA File Number	67507
------------	-----	-----------------	-------

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 1.500-1.740: Bale Length: 5: Mesh Length: 18
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 1,680

