



FCSD70: Service Drop, Closed Mesh, Single Eye, Cable Diameter 0.70 - 0.97 inches, Bale Length 8-in, Mesh Length 9-in, Break Strength 1020 lbs.

## Features & Benefits

Service drop grips provide support for utility distribution lines from service pole to building or from pole to pole.

They are offered with either the single eye or locking bale attachment.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

They can also be used for cable TV and fiber optic cable support.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Bale Length: 8: Mesh Length: 9

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007131703
Country Of Origin	Mexico	Construction	Support and Strain Relief Grips, Various Types of Pulling
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)
Type	Support Grip		

### Dimensions

Product Width US	0.85 in	Product Length US	6.75 in
Mesh Length	6.75 in	Cable Diameter Range	0.730-0.850 in

### Technical Information

Approximate Break Strength	1400 lb	Maximum Cable Range	0.7 in
Eye Style	Single	Minimum Cable Range	0.97 in
Capacity	Various Cable Diameter Ranges	Indoor/Outdoor	Both
Mounting	Consult the Factory for Mounting Recommendations		