



Standard duty, Split rod, Single eye. Cable diameter - 1.500-1.740-inch, Bale length - 12-inch, Mesh length - 20-inch, Break strength - 2,640 lbs.

Features & Benefits

Split rod support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Split rod support grips are used when the end of the cable cannot be easily accessed and the installation is temporary.

Support grips are woven of corrosion-resistant tinned-bronze wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

| | | | |
|--------------------|----------------|--------------|---|
| Product Line | Pass & Seymour | UPC Number | 785007982909 |
| Country Of Origin | Mexico | Construction | Various Types of Pulling, Support and Strain Relief Grips |
| Application Sector | Industrial | Standard | UL/CSA Approval (consult factory) |

Technical Information

| | | | |
|----------|--|------------|---|
| Capacity | Various Cable Diameter Ranges | Cable Size | Cable Dia. Range: 1.500-1.740: Bale Length: 12: Mesh Length: 18 |
| Mounting | Consult the Factory for Mounting Recommendations | Load | Approx. Break Strength: 1,680 |