



FR175LB: Standard Duty, Split Rod, Locking Bale (Universal Eye), Cable Diameter 1.75 - 1.99 inches, Bale Length 14-in, Mesh Length 17-in, Break Strength 3150 lbs.

Features & Benefits

Split rod support grips are used when the end of the cable cannot be easily accessed and the installation is temporary.

Split rod support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-stainless steel wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Bale Length: 14: Mesh Length: 17

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007982251
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Maximum Cable Range	1.75 in	Minimum Cable Range	1.99 in
Capacity	Various Cable Diameter Ranges	Mounting	Consult the Factory for Mounting Recommendations