



Standard-duty, Split lace, Locking bale (universal eye). Cable diameter - 1.000-1.240-inch, Bale length - 18-inch, Mesh length - 15-inch, Break strength - 1,920 lbs.

## Features & Benefits

Split lace support grips are designed for loads up to 600 lbs.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-bronze wire.

Vertical runs of no more than 100 ft.

Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

## Specifications

### General Info

Product Line	Pass & Seymour	UPC Number	785007983548
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

### Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 1.000-1.240: Bale Length: 18: Mesh Length: 15
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 1,920