



Standard duty, Split lace, Locking bale (universal eye). Cable diameter - 1.500-1.740-inch, Bale length - 18-inch, mesh length - 18-inch, Break strength - 1,920.

## Features & Benefits

Split lace support grips are designed for loads up to 600 lbs.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Support grips are woven of corrosion-resistant tinned-bronze wire.

Vertical runs of no more than 100 ft.

Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

## Specifications

### General Info

|                    |                |              |   |
|--------------------|----------------|--------------|---|
| Product Line       | Pass & Seymour | UPC Number   | 785007983562  |
| Country Of Origin  | Mexico         | Construction | Various Types of Pulling, Support and Strain Relief Grips |
| Application Sector | Industrial     | Standard     | UL/CSA Approval (consult factory)                         |

### Technical Information

|          |  |            |   |
|----------|--|------------|---|
| Capacity | Various Cable Diameter Ranges                    | Cable Size | Cable Dia. Range: 1.500-1.740: Bale Length: 18: Mesh Length: 18 |
| Mounting | Consult the Factory for Mounting Recommendations | Load       | Approx. Break Strength: 1,920                                   |