



Pass and Seymour

Support Grips Standard Duty, Split Lace

Part No. FS200U

Standard-duty, Split lace, single eye. Cable diameter - 2.000-2.490", Bale length - 16", Mesh length - 22", Break strength - 3,760 lbs.



Features & Benefits

Split lace support grips are designed for loads up to 600 lbs.

Vertical runs of no more than 100 ft.

They are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing.

Split lace support grips are used when the end of the cable cannot easily be accessed and the support grip is intended for permanent installation.

Support grips are woven of corrosion-resistant tinned-bronze wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

UPC Number 785007984248

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Industrial

Construction Various Types of Pulling, Support and Strain Relief Grips

Standard UL/CSA Approval (consult factory)

Technical Information

Mounting Consult the Factory for Mounting Recommendations

Cable Size Cable Dia. Range: 2.000-2.490; Bale Length: 16; Mesh Length: 22

Capacity Various Cable Diameter Ranges

Load Approx. Break Strength: 3,760