



Pass and Seymour
Support Grips Heavy Duty
Part No. FSHL350UU

Heavy-duty, Split lace, Double eye. Cable diameter - 3.500-3.990-inch, Bale length - 10-inch, Mesh length - 47-inch, Break strength - 13,120 lbs.



Features & Benefits

Heavy-duty support grips feature a double weave mesh and are available in a variety of eye styles and cable ranges for supporting electrical and fiber optic cable, metal rods, and tubing. Support grips are woven of corrosion-resistant tinned-bronze wire.

Most Flexcor products have UL and/or CSA approvals. Please contact factory for approval information.

Specifications

General Info

Product Line	Pass & Seymour	UPC Number	785007985023
Country Of Origin	Mexico	Construction	Various Types of Pulling, Support and Strain Relief Grips
Application Sector	Industrial	Standard	UL/CSA Approval (consult factory)

Technical Information

Capacity	Various Cable Diameter Ranges	Cable Size	Cable Dia. Range: 3.500-3.990: Bale Length: 10: Mesh Length: 45
Mounting	Consult the Factory for Mounting Recommendations	Load	Approx. Break Strength: 13,120