



Wattstopper
0-10V PIR IN FIXTURE SENSOR BLE120-277V
Part No. FSP-311



The FSP-3x1 sensors provide continuous dimming intensity control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting unlimited sensor profiles. The FSP-3x1 family is available in three different voltage configurations adding flexibility to your fixture design or project.

Features & Benefits

Designed for LED fixtures and rated for extreme temperatures

Hold off setpoint with automatic calibration option for convenience and added energy savings

Adjustable via the iOS® or Android® Sensor Configuration App

Adjustable time delay and cutoff delay

Fully adjustable high and low dimmed light levels

Continuous dimming for Energy Code Compliance

Choice of four lenses for mounting heights from 8 ft. to 40 ft.

Specifications

General Info

Product Line	Wattstopper	UPC Number	754182943685
Country Of Origin	China		