



Wattstopper
0-10V PIR Straight Mount Sensor, BLE, 120-277V, 40 ft Lens, Black
Part No. FSP-311B-S-L7-B



The FSP-3x1B sensors provide continuous dimming light level control based on motion and/or daylight contribution. They control 0-10 VDC LED drivers or dimming ballasts, as well as non-dimming ballasts and, with an FSP-Lx Lens, are rated for wet and cold locations. All control parameters are adjustable via the iOS or Android Sensor Configuration App capable of storing and transmitting sensor profiles. The FSP-3x1B family is available in three configurations for mounting inside a fixture, to the outside of a fixture via a 1/2" knockout, or to a pole.

Features & Benefits

Designed for LED fixtures and rated for extreme temperatures; options for box or pole mounting

Hold off setpoint with automatic calibration option for convenience and added energy savings

Adjustable via the iOS® or Android® Sensor Configuration App

Adjustable time delay and cutoff delay

Fully adjustable high and low dimmed light levels

Continuous dimming & daylight harvesting for energy efficiency and energy code compliance

IP66 rated with choice of lenses for wet and outdoor locations, and mounting heights from 8' to 40'

Specifications

General Info

Color	Black	UPC Number	754182941438
Country Of Origin	China	Product Line	Wattstopper