



Shielded Category 6A field terminable PCB wired 8 position modular plugs, able to be terminated to either T568A or B wiring, 5 pack of plugs, no special tools required. Supports 22-26AWG solid conductors and 23-26AWG stranded conductors. Installer friendly lacing sled with attached wiring label supports accurate IDC termination with parallel joint pliers. Printed circuitry offers better control and eliminate noise between conductors and 50 micro inch plated plug contacts. Supports up to 5 re-terminations. Condense size of the terminated plug makes this plug compatible with most modular applications. Qualified to 1.5 amps for PoE applications.

Features & Benefits

Easy lacing wire sled	Easy to follow attached universal wiring label
Internal printed circuitry	Parallel joint pliers and cutters are the only tools required
RoHS compliant	Rated for 1.5+ amps

Specifications

General Info

Product Line	Ortronics	Replaced by Part Number	HDPSC6A-5PK
Hazardous Materials	No	UPC Number	662875026341
Country Of Origin	China	Standard	UL 1863, 2043

Dimensions

Product Width US	0.55 in	Product Depth US	2.67 in
Product Height US	0.49 in		

Technical Information

Category Performance Rating	Cat6a	Compatibility	Stranded or Shielded Cable
Plating Specification	POE+ and 4PPoE Certified	Shielded/Unshielded	Shielded