



Ortronics
Telecommunications Ground Bar
Part No. GB2X10TGB



Manufactured of 1/4 in thick electrolytic tough pitch 110 alloy copper bar. Includes 1-1/2 in insulators and 1 in offset stainless steel mounting brackets. Includes one 1/2 oz. tube of antioxidant joint compound. Meets BICSI and ANSI/TIA-607 standards. Kits include: (1) Copper bonding bar with brackets and insulators, (6) #6 compression lugs, (3) #2 compression lugs, (1) 2/0 compression lug, (1) 4/0 compression lug, (12) 1/4 in-20 x 3/4 in SS hex head cap screw, (12) 1/4 in-20 SS lock washer, (12) 1/4 in-20 SS hex nut, (6) 3/8 in-16 x 1 in SS hex head cap screw, (6) 3/8 in-16 SS lock washer, (6) 3/8 in-16 SS hex nut.

Features & Benefits

Manufactured of 1/4" thick electrolytic tough pitch 110 alloy copper bar

Meets BICSI an EIA/TIA 607 standards

Includes one 1/2 oz. tube of antioxidant joint compound

Includes 1-1/2" insulators and 1" off-set stainless steel mounting brackets

Specifications

General Info

Product Line	Ortronics	Color	Metal
UPC Number	662875665205	Country Of Origin	United States
Application Sector	Commercial	Standard	BICSI;ANSI/TIA- 607
Warranty Type	5-Year	Type	Ground Bar

Dimensions

Product Width US	10.0 in	Product Depth US	3.0 in
Product Height US	2.0 in	Screw Size	1 in

Additional Information

RoHS Compliant	Yes
----------------	-----

Technical Information

Termination Style	Screw Terminal	Conductor Size	3 AWG
Number of Holes	18	Conductor Material	Copper
Mounting	Screw Down		