



**Ortronics**  
**Telecommunications Ground Bar**  
Part No. GB2X10TGB



Manufactured of 1/4 in thick electrolytic tough pitch 110 alloy copper bar. Includes 1-1/2 in insulators and 1 in offset stainless steel mounting brackets. Includes one 1/2 oz. tube of antioxidant joint compound. Meets BICSI and ANSI/TIA-607 standards. Kits include: (1) Copper bonding bar with brackets and insulators, (6) #6 compression lugs, (3) #2 compression lugs, (1) 2/0 compression lug, (1) 4/0 compression lug, (12) 1/4 in-20 x 3/4 in SS hex head cap screw, (12) 1/4 in-20 SS lock washer, (12) 1/4 in-20 SS hex nut, (6) 3/8 in-16 x 1 in SS hex head cap screw, (6) 3/8 in-16 SS lock washer, (6) 3/8 in-16 SS hex nut.

## Features & Benefits

Manufactured of 1/4" thick electrolytic tough pitch 110 alloy copper bar

Meets BICSI an EIA/TIA 607 standards

Includes one 1/2 oz. tube of antioxidant joint compound

Includes 1-1/2" insulators and 1" off-set stainless steel mounting brackets

## Specifications

### General Info

Product Line	Ortronics	UPC Number	662875665205
Country Of Origin	United States	Application Sector	Commercial

### Dimensions

Product Width US	10.0 in	Product Depth US	3.0 in
Product Height US	2.0 in		

### Additional Information

RoHS Conformant	Yes
-----------------	-----