



Manufactured of 1/4 in thick electrolytic tough pitch 110 alloy copper bar. Includes 1-1/2 in insulators and 1 in offset stainless steel mounting brackets. Includes one 1/2 oz. tube of antioxidant joint compound. Meets BICSI and ANSI/TIA-607 standards. Kits include: (1) Copper bonding bar with brackets and insulators, (6) #6 compression lugs, (3) #2 compression lugs, (1) 2/0 compression lug, (1) 4/0 compression lug, (12) 1/4 in-20 x 3/4 in SS hex head cap screw, (12) 1/4 in-20 SS lock washer, (12) 1/4 in-20 SS hex nut, (6) 3/8 in-16 x 1 in SS hex head cap screw, (6) 3/8 in-16 SS lock washer, (6) 3/8 in-16 SS hex nut.

Features & Benefits

Manufactured of 1/4" thick electrolytic tough pitch 110 alloy copper bar

Includes 1-1/2" insulators and 1" off-set stainless steel mounting brackets

Specifications

General Info

Product Line	Ortronics	UPC Number	662875665250
Country Of Origin	United States	Application Sector	Commercial

Dimensions

Product Width US	12.0 in	Product Depth US	3.0 in
Product Height US	4.0 in		

Additional Information

RoHS Conformant	Yes
-----------------	-----